


# Komplet diagram



# Stykliste

RE1	1E0 x 11	
RE2	1E0 x 11	
R1	40E2	
R2	40E2	
R7	2E20	
R8	2E20	
R15	22E1	
R16	22E1	
R27	10k (Single end) eller 301E (Balanceret)	
R28	0E (Single end) eller 301E (Balanceret)	
R34	33k2	
RCND	2E20	
P1	500E Bourns trimmer mrk. 501	
P2	10k Bourns trimmer mrk. 103	
C1	10uF Metaliseret polyprop.	
C2	0,22uF MKT	
C3	10uF Metaliseret polyprop.	
C4	0,22uF MKT	
C6	470uF LXF low ESR	
C7	0,22uF MKT	
C8	0,22uF MKT	
C9	470uF LXF low ESR	
C10	56p Polyethylen eller styroflex	
C12	470uF LXF low ESR	
C13	470uF LXF low ESR	
C14	470uF LXF low ESR	
C15	470uF LXF low ESR	
D3	BAV21 200 ultrafast signal diode	
D4	BAV21 200 ultrafast signal diode	
T1	25C2922	NB. Alle udgange i sættet skal være matchede!
T2	25A1216	NB. Alle udgange i sættet skal være matchede!
T3	25A1038E	Rohm
T4	25C2389E	Rohm
T5	25C4278E	Rohm
T6	25A1633E	Rohm
T7	25D1763A	Rohm
T8	25B1186A	Rohm